

Raven Vertical Fiberglass Liquid Pump Tank- 1000 Gallon

Mfg: Raven

Model:

Stock No.: RPCN079.3a

Serial No.:

Raven Vertical Fiberglass Liquid Pump Tank- 1000 Gallon. Inside straight-wall dimensions: 5 ft. dia. x 6 ft. 11-1/2 in. H. (2) Teel Centrifugal Pumps, Model: 3P607, impeller diameter: 5-1/2 in. (2) Dayton Motors, 5 hp, 3495 rpm, 208-230/460 V, 14.4-12.8/6.4 amps, 60 Hz, 3 phase. Jo-Bell Products External Liquid Level Control, Model: R-23, S/N: 111178. Type: R23, max pressure: 30 psig, maximum specific gravity: 0.8, max temperature: 250-400°F. Inlets: (1) 5 in. dia. product infeed. Outlets: (1) 4 in. dia. overflow port, (1) 1-1/2 in. dia. port, (2) 1-1/2 in. dia. discharge ports. Overall dimensions: 10 ft. 7-1/2 in. L x 7 ft. W x 7 ft. 1/2 in. H.







