

Tri Clover Model PRRED25 Positive Displacement Pump

Mfg: Tri Clover

Model: PRRED25-11/2M-YC4-SL

Stock No: RPCN159.6

Serial No: 180672-01

Tri Clover Model PRRED25 Positive Displacement Pump. Model: PRRED25-11/2M-YC4-SL. S/N: 180672-01. Flow rate for new pump is 28 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Sew Eurodrive motor. 2 hp, 1720 rpm, 230/460 V, 6.2/3.1 amps, 60 Hz, 3 phase. Sew Eurodrive speed reducer. Ratio: 4.32:1, rpm in: 1720, rpm out: 398, torque: 317 lb-in, service factor: 3.5. Inlet: (1) 1-1/2 in. dia. S-line fitting. Outlet: (1) 1-1/2 in. dia. S-line fitting. Overall dimensions: 3 ft. 1-1/2 in. L x 11-1/2 in. W x 1 ft. 2-1/2 in. H.





