

## Mycom 6-Cylinder Reciprocating Compressor – 50 HP

Mfg: Mycom

Model: 6J

Stock No.: RPCN200.5

Serial No.: 11914

Mycom 6-Cylinder Reciprocating Compressor – 50 HP. Model: 6J. S/N: 11914. Capacity: 75 tons of R-22 with a 40°F Suction, 105°F Discharge, 15°F Superheat, and 0°F Subcooling at a max rpm of 1450 and at 72.9 BHP. Refrigerant: Freon (R-12, R-22, R-404, and R-502.) Leak test pressure (hi/lo): 313/185. Hydrostatic test pressure (hi/lo): 470. Lincoln Electric Motor. 50 hp, 1770 rpm, 230/460 V, 125/62.5 amps, 60 Hz, 3 phase. Drive pulley diameter: 11-1/2 in. Driven pulley diameter: 16 in. Pulley ratio: 0.71. Final rpm: 1272. AC&R Oil Separator-3 Gallon. Model: S-5202. Straight-wall dimensions: 8 in. dia. x 1 ft. 2 in. H. Inlet: (1) 2-1/2 in. dia. (refrigerant suction). Outlet: (1) 2 in. dia. (refrigerant discharge). Overall dimensions: 6 ft. 4 in. L x 3 ft. 8 in. W x 3 ft. 6-1/2 in. H. (ACN211a-BC/Motor).









