

## Mycom 8-Cylinder Reciprocating Compressor

Mfg: Mycom

Model: F62A

Stock No.: RPCN389.11

Serial No.: 19570

Mycom 8-Cylinder 2-Stage Compound Reciprocating Compressor. Model: F62A. S/N: 19570. Refrigerant: Set up for use with Freon, R22, R502, R12. Leak test pressure (hi/lo): 313/185 psig. Hydrostatic test pressure (hi/lo) 470 psig. Displacement: 165 cfm low stage and 55 cfm high stage. Oil Separator: 2 Gallon, inside straight-wall dimensions: 8 in. dia. x 11 in. H. Lincoln Electric Motor, 60 hp, 1775 rpm, 230/460 V, 154/77 amps, 60 Hz, 3 phase. Drive pulley diameter: 11-1/2 in. Driven pulley diameter: 1 ft. 4 in. Pulley ratio: 0.71. Final rpm: 1260. Inlets: (1) 3 in. dia. compressor suction port, (1) 1-1/2 in. dia. water infeed port. Outlets: (2) 1-1/2 in. dia. water discharge port, (1) 2 in. dia. refrigerant discharge port. Overall dimensions: 7 ft. 9 in. L x 4 ft. 3 in. W x 7 ft. H.(ACN229a-BC/Motor).



