

Viking Rotary Pump Positive Displacement Pump

Mfg: Viking® Pump

Model: K125

Stock No: RWDG075

Serial No: 2200062

Viking Rotary Pump Positive Displacement Pump. Model: K125. S/N: 2200062. Sew-Eurodrive Motor, 2 hp, 1720 rpm, 230/460 V, 6.2/3.1 amps, 60 Hz, 3 phase. Sew-Eurodrive Drive, ratio: 42.90, final speed: 10.8/54 rpm, torque: 1490 lb.-in. Inlets: (1) 2-1/2 in. dia. port. Outlets: (1) 2 in. dia. FNPT. Overall dimensions: 3 ft. 4 in. L x 1 ft. 8 in. W x 2 ft. 10 in. H.





