

Vilter Rotary Screw Compressor Package

Mfg: Vilter

Model: VRS-3400

Stock No. 500-SC-8731a

Serial No. 434

Vilter Rotary Screw Compressor Package. Model: VRS-3400. S/N: 434. Order No: F91890-3. Refrigerant: ammonia. Design pressure (hi/lo): 250/250 psig. Power supply: 120 V. Howden Rotary Screw Compressor, S/N: MK4E/WRV32/16526/434, Contract No: JH3774, maximum speed: 3600 rpm, hydraulic test pressure: 609 psi, maximum working pressure (hi/lo): 250/60 psi. Vilter Oil Separator. Lufkin Gears Speed Reducer, input horsepower: 1350 hp, ratio: 2.991. 1992 American Precision Type 500 Basco Shell and Tube Heat Exchanger, shell side MAWP: 300 psi @ 300 °F, tube side MAWP: 150 psi @ 300 °F. Inlets: (1) 8 in. dia. refrigerant suction port. Outlets: (1) 6 in. dia. refrigerant discharge port. Overall dimensions: 12 ft. 5 in. L x 108 in. W x 106 in. H. (ACN613).





