

APV R-Series Positive Displacement Pump

Mfg: APV

Model: R6R

Stock No: SCJC163.11

Serial No: G-8768

APV Positive Displacement Pump. Size: R6R. S/N: G-8768. Flow rate for new pump is 240 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Leroy-Somer motor: 7.5 hp, 1740 rpm, 208/230/460 V, 20.6/19.2/9.6 A, 60 hz, 3 phase. Leroy-Somer motor drive: 3.95 ratio, 443 final rpm. (2) 5-5/8 in. rubber impellers. Mild steel base mounted. Inlet/outlet: (2) 3 in. S-Line. Overall dimensions: 3 ft. 8-1/2 in. L x 1 ft. 8 in. W x 1 ft. 7-1/2 in. H.







