

APV R-Series Positive Displacement Pump

Mfg: APV

Model: R6BS

Stock No: SCJC164.11

Serial No: P-8192-0298

APV R-Series Positive Displacement Pump. Model: R6BS. S/N: P-8192-0298. Flow rate for new pump is 240 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Baldor Industrial Motor: 7.5 hp, 1760 rpm, 208-230/460 v, 21.4-20.4/10.2 a, 60 Hz, 3 phase. (2) 5-5/8 in. rubber rotors. (1) Viking Pump, Inc. helical gear reducer: part no: 3-551-003-419-GD. (1) Hubbell® Disconnect switch: Cat no. HBLDS3, 30 AMP, 600 VAC Max. Mild steel base. Inlet/outlet: (2) 3 in. S-Line. Overall dimensions: 3 ft. 10 in. L x 1 ft. 9 in. W x 3 ft. 5 in. H.







