

United State Steel Corporation Horizontal Ammonia Receiver Tank – 2009 Gallons

Mfg: United State Steel Corporation

Model:

Stock No: SCJC518.15

Serial No: 120590

United State Steel Corporation Horizontal Ammonia Receiver Tank. S/N: 120590. Listed capacity: 2009 gallons. Tank dimensions: 4 ft. dia. x 24 ft. L. MAWP 250 psig @ 650°F. (1) 1-3/4 in. top hand valve, (1) 3 in. Henry hand valve, (2) 1-1/2 Hansen Technologies pressure relief valves. Inlet / outlets:(2) 1 in., (2) 1-1/2 in., bottom drain 1 in. hand valve. Overall dimensions: 24 ft. 2 in. L x 4 ft. W x 6 ft. 7 in. H.





**CAPACITY
2009 GAL.**

ASME
UNF. RED. PRESS. RELIEF VALVE
XXXXXXXXXX
SERIAL NO. 120590 YEAR 75
250/650°F
2009 HEAD 415
AMERICAN BRIDGE DIVISION
UNION BRIDGE STEEL CO.
PITTSBURGH, PA.

Pressure-Relief Valve
Cat. No.: H5602
Air Capacity: 768 SCFM
Set Pressure: 250 PSI
Size: Inlet Outlet
Inch: 1/4 1/2
Serial No.: 120590
HANSEN TECHNOLOGIES CORPORATION

Pressure-Relief Valve
Cat. No.: H5602
Air Capacity: 768 SCFM
Set Pressure: 250 PSI
Size: Inlet Outlet
Inch: 1/4 1/2
Serial No.: 120590
HANSEN TECHNOLOGIES CORPORATION U.S.A.