



Engineering Data

Do not use for construction. Refer to factory certified dimensions.

This brochure includes data current at the time of publication which should be reconfirmed at the time of purchase.



MODEL NO.	APPROX. SHIPG. WEIGHT	APPROX. OPER. WEIGHT	HEAVIEST SECTION (Cell)	CFM	MOTOR HP (0" ESP)	GPM	PUMP MOTOR HP	R-717 CHARGE (LBS.)	REMOTE SUMP			
									BOTTOM DRAIN SIZE	APPROX. OPER. WEIGHT	F	H
C2710-A	1070	1380	1070"	2900	1/8	35	1/8	19	2 1/2	1140	14 1/4	79 3/8
C2711-C	1260	1580	1260"	3800	3/8	35	1/8	25	2 1/2	1340	22 3/4	96 3/8
C2712-D	1420	1760	1000	4400	1	35	1/8	32	2 1/2	1520	31 1/4	104 7/8
C2712-F	1470	1810	1050	5300	2	35	1/8	34	2 1/2	1570	31 1/4	104 7/8
C2720-F	1850	2550	1850"	8200	2	75	1/2	35	3	2090	13 1/4	88 3/8
C2721-F	2100	2810	2100"	8900	2	75	1/2	45	3	2350	21 1/4	96 3/8
C2722-F	2390	3190	1650	8500	2	75	1/2	61	3	2670	30 1/4	105 3/8
C2722-G	2440	3180	1700	10000	3	75	1/2	65	3	2720	30 1/4	105 3/8
C2723-G	2700	3480	1940	9600	3	75	1/2	76	3	3020	38 3/4	113 3/8
C2723-H	2770	3550	2010	11600	5	75	1/2	80	3	3090	38 3/4	113 3/8
C2732-G	3670	4880	2400	12100	3	115	3/4	90	4	4230	33 1/4	117 3/8
C2732-H	3740	5050	2470	14500	5	115	3/4	100	4	4300	33 1/4	117 3/8
C2733-H	4160	5270	2850	14000	5	115	3/4	110	4	4520	42 1/2	126 3/8
C2742-H	4600	6370	3080	19600	5	150	1	120	6	5360	33 1/4	117 3/8
C2742-J	4680	6450	3140	22000	7 1/2	150	1	130	6	5440	33 1/4	117 3/8
C2743-J	5230	7060	3640	21000	7 1/2	150	1	145	6	6050	42 1/2	126 3/8
C2842-H	7130	8920	4920	25900	5	220	1 1/2	170	6	7510	33 1/4	129 3/8
C2842-J	7220	9010	5830	28300	7 1/2	220	1 1/2	190	6	7580	33 1/4	129 3/8
C2843-J	8120	9930	5930	28000	7 1/2	220	1 1/2	210	6	8510	42 1/2	138 3/8
C2844-K	8770	10580	6580	30100	10	220	1 1/2	245	6	9160	51 3/4	147 3/8
C2442-K	10450	13930	7050	44750	10	385	3	290	8	11870	33 1/4	141 3/8
C2443-K	11860	15380	8460	43400	10	385	3	360	8	13420	42 1/2	151 3/8
C2444-L	13310	16970	9660	48550	15	385	3	430	8	15010	51 3/4	160 3/8
C2462-L	15170	20260	10390	67650	15	580	5	435	10	17250	33 1/4	153 3/8
C2463-L	17350	22650	12570	65700	15	580	5	540	10	19640	42 1/2	163 3/8
C2464-L	19530	25050	14750	64200	15	580	5	645	10	22040	51 3/4	172 3/8
C2464-M	19540	25060	14750	70500	20	580	5	645	10	22050	51 3/4	172 3/8

*Unit normally ships in one piece.