

Quincy Rotary Screw Air Compressor

Mfg: Quincy

Model: SI04ACA3MG

Stock No. SDYC005.

Serial No. 93317

Quincy Rotary Screw Air Compressor. Model: SI04ACA3MG. S/N: 93317. Natd Bd: 93268. M.A.W.P. 175 psi @ 450 °F. MDMT: -20 °F @ 175 psi. Lincoln Motor, 100 hp, 1785 rpm, 230/460 V, 250/125 amps, 60 Hz, 3 phase, (1) 24 in. dia. fan with a Baldor Motor, 5 hp, 1750 rpm, 230/460 V, 13.2/6.5 amps, 60 Hz, 3 phase. Quincy Auto-Dual Control. Compressor run time: 20263 hrs. Inlets: (1) 2 in. dia. bevel. Overall dimensions: 104 in. L x 60 in. W x 67-1/2 in. H.



