

Mycom 8 - Cylinder Reciprocating Compressor

Mfg: Mycom

Model: 8 J

Stock No.: SFEP1249.1

Serial No.: 12132

Mycom 8 - Cylinder Reciprocating Compressor. Model: 8 J. S/N: 12132. Refrigerant: set up for Freon, R-12, R-22, R-404, R-502. Capacity: 99.9 Tons of R-22 at 97.2 BHP with a 40°F suction temperature, 105°F discharge temperature and a 15°F superheat. Leak pressure (hi/lo): 313/185 psi. Hydrostatic test pressure hi/lo: 470/470 psi. Heat exchanger: 4 in. diameter x 21 in. L. Control box. 6-Belt pulley. Inlet: 3 in. diameter, square flange: 5-1/2 in. L x 5-1/2 in. W., (4) hole, center-to-center: 6 in. L. Outlet: 2-1/2 in. diameter, square flange: 6-1/2 in. L x 6-1/2 in. W., (4) hole, center-to-center: 6-1/2 in. L. Compressor dimensions 3 ft. L x 2 ft. 9 in. W x 2 ft. 8 in. H. Overall dimensions: 7 ft. 11 in. L x 3 ft. 9 in. W x 4 ft. 5 in. H.(ACN190-BC).

