

Graco Senator Air Powered Drum Pump

Mfg: Graco

Model: C96J

Stock No. SGMB076.2

Serial No. W188

Graco Senator Air Powered Drum Pump. Model: C96J. S/N: W188. P/N: 948292. Maximum capacity: 13.8 gpm. Maximum air pressure: 100 psig. Ratio: 14 ft. Luftmotor Air Motor, Model: H96B, S/N: W253, P/N: 624250. Graco Base, Model: J96E, S/N: W156, P/N: 947-992. Plate diameter: 20 in. Inlets: (1) 2 in. dia. suction port. Outlets: (1) 1 in. dia. S-line fitting. Overall dimensions: 2 ft. 9 in. L x 1 ft. 2 in. W x 7ft. 5-1/2 in. H.

