

Grieve Heat Treating Oven

Mfg: Grieve

Model: AF-850

Stock No: SGML025.1

Serial No: 370146

Grieve Heat Treating Oven. Model: AF-850. S/N: 370146. Heat input: 12 kW. Oven dimensions: 36 in. x 22-1/2 in. x 22-1/2 in. Max temperature: 850 °F. Electrical requirements: 460 V, 17 amps, 60 Hz, 3 phase. Howell Motor: 1/3 hp, 1725 rpm, 208-220/440 V, 2.2/1.1 amps, 60 Hz, 3 phase. Unit features a Grieve digital set-point controller, excess temperature control and Eagle signal timers for the blower, heater and damper. Inlets: (1) 3-1/2 in. port with pneumatic knife gate. Overall dimensions: 72 in. L x 42 in. W x 72 in. H.





