

Waukesha 30 Positive Displacement Pump


Mfg: Waukesha






Model: 30




Stock No: SGMN122B.13a

Serial No: 234534

Waukesha Positive Displacement Pump. Model: 30. S/N: 234534. Flow rate for new pump is 36 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Reliance Electric motor: 1 hp, 1725 rpm, 230/460 v, 2.8/1.4 a, 60 Hz, 3 phase. (2) 4-3/8 in. rotors. Inlet/outlet: (2) 1-1/2 in. ACME. Overall dimensions: 3 ft. 1-1/2 in. L x 1 ft. W x 1 ft. 2 in. H.







Pirelli
 CE
 A
 Pirelli Domireb Company
 SERIAL NO. 234534 99
 MODEL 030
 READ AND UNDERSTAND INSTRUCTION MANUAL BEFORE

RELIANCE ELECTRIC XEX
 DUTY MASTER A.C. MOTOR XT EXTRA TOUGH
 FR TYPE PH
 HP RPM VOLTS AMPS HZ SF
 CE
 PREMIUM EFFICIENCY
 RELIANCE ELECTRIC INDUSTRIAL COMPANY
 CLEVELAND, OHIO 44117