

## Semco Rotary Valve

Mfg: Semco

Model: RV-04

Stock No: SGMN126.1a

Serial No: 872801

Semco Rotary Valve. Model: RV-04. S/N: 872801. SEW Eurodrive motor, 3/4 hp, 1700 rpm, 230/460 V, 3.0/1.5 amps, 60 Hz, 3 phase. SEW Eurodrive gear reducer, ratio: 68.71:1, output: 25 rpm, 1890 lb. in., Type: R600T80K4. Motor sprocket: 4 in. Valve sprocket: 6 in. Sprocket ratio: 1.5:1. Final rpms at valve: 17 rpms. Flange Inlet ID: 10 in. L x 9 1/2 in. W. Flange Inlet OD: 15 in. L x 13 1/2 in. W. Outlet diameter: 10 in. Overall dimensions: 2 ft. 3 in. L x 2 ft. W x 1 ft. 5 in. H.





