

Moyno FG-Series 2-stage Sanitary Pump

Mfg: Moyno

Model: 2FG8

Stock No. SHCA1542.4

Serial No.

Moyno FG-Series 2-stage Sanitary Pump. Model: 2FG8. Type SSG-AAA. Stainless Steel Construction. Capacity: 7.2 gpm. Displacement per Revolution: 0.07 gal. 304 Stainless Steel suction housing. 316 Stainless Steel internal parts include drive shaft, pins, connecting rod, rotor, and other minor metallic parts in contact with product. 416 Stainless Steel stator. Extra large bearings and bearing housing to handle increased loads. Designed for highly viscous fluids @ low flow rates with high pressure. Reliance Electric Motor, 7.5 hp, 1760 rpm, 230-460 V, 21-10.5 amps, 60 Hz, 3 phase. Reliance Master XL Gearmotor, 17.1 ratio, 102.9 output rpm. Unit is equipped with a 5 in. dia. x 40 in. L shaft and a 4 in. dia. x 40 in. L screw auger. Overall dimensions: 8 ft. 6 in. L x 2 ft. 2 in. W x 2 ft. 7 in. H.



