

APV Crepaco R-series Positive Displacement Pump

Mfg: APV Crepaco

Model: R6R

Stock No: SHCA904.1a

Serial No: G-4748

APV Crepaco R-series Positive Displacement Pump. Model: R6R. S/N: G-4748. Flow rate for new pump is 240 gpm at required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Sew-Eurodrive motor, 5 hp, 1680 rpm, 230/460 V, 13.6/6.8 amps. Sew-Eurodrive, ratio: 26.06, torque 5310 lb-in., provides a final rpm of 64. Features include: complete parts interchangeability, easy disassembly and cleanup, and low maintenance. Typical applications include: fruit cocktails, yogurt, alcoholic beverages, dough, chocolate syrup and shampoo. Inlets/outlets: (2) 3 in. dia. ACME fittings. Overall dimensions: 3 ft. 9 in. L x 1 ft. 7 in. W x 1 ft. 11 in. H.(ACN116).





