

Chemcom Rotary Pumps

Mfg: Chemcom

Model: 1170-90-T3D and 1120-90-T3D

Stock No. SHCA932.2a

Serial No. 22843 and 21028

Chemcom Rotary Pumps. Models: 1170-90-T3D and 1120-90-T3D. S/N's: 22843 and 21028. Capacity: 250 gpm @ 35 psig (sn: 22843) and 8 gpm @ 100 psig (sn: 21028). Baldor Industrial Motor, 1 hp, 1725 rpm, 230/460 V, 3.4/1.7 amps, 60 Hz. Reeves Variable Speed Module, Max. 3320 and Min. 644. Inlets: (1) 1-1/2 in. dia. port, (1) 1/2 in. dia. port. Outlets: 1-1/2 in. NPT, (1) 1/2 in. port. Overall dimensions: 49 in. L x 24 in. W x 53-1/2 in. H.



