

Waukesha 130 Positive Displacement Pump

Mfg: Waukesha

Model: 130

Stock No. SHCA938.9

Serial No. 106411

Waukesha 130 Positive Displacement Pump. Model: 130. S/N: 106411. Pumping capacity: 75 gpm. Nominal capacity: 150 gpm. Displacement per revolution: 0.254 gal. Maximum speed: 800 rpm. Vented cover. Seal option: o-ring. Sew-Eurodrive Motor, 7.5 hp, 1720 rpm, 230/460 V, 14.2/9.6 amps, 60 Hz, 3 phase. Sew-Eurodrive Gear Drive, ratio: 5.89, torque 1620, 292 rpm (final). The 130's non-galling '88' alloy rotors provide minimum breakage on fluids with discrete particles such as diced tomato products. Waukesha sanitary pumps feature easy cleaning and disassembly. Typical products handled by Waukesha pumps include products from bakery, beverage, canning, confectionary, cosmetics, dairy, meat packaging, and pharmaceutical industries. Inlets/outlets: (2) 3 in. S-line fitting ports. Overall dimensions: 52-1/2 in. L x 13-1/2 in. W x 20 in. H.





