

APV R6 Series Positive Displacement Pump

Mfg: APV

Model: R6RIHD

Stock No: SIBI147F.10

Serial No: PP-1940-0499

APV R6 Series Positive Displacement Pump. Model: R6RIHD. S/N: PP-1940-0499. Flow rate for new pump is 240 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Reliance Electric motor: 10 hp, 1755 rpm, 230/460 volts, 25.4/12.7 amps, 60 Hz, 3 phase. Motor drive is capable of 5.0 ratio, 1750/350 rpm in/out, 3495 torque. (2) Rotating rotors. Inlets: (1) 10 in. flange with (12) mounting holes 7/8 in. diameter. 3-5/8 in. adjacent and 14-1/4 in. opposite. (2) 2 in. S-line. Outlet: (1) 3 in. S-line. Overall dimensions: 5 ft. L. x 1 ft. 10 in. W. x 2 ft. 3-1/4 in. H.(ACN170).



