

## Waukesha Model 034 Positive Displacement Pump

**Mfg: Waukesha**

**Model: 034**

**Stock No: SKFI033.19**

**Serial No: 87097 SS**

Waukesha Model 034 Positive Displacement Pump. S/N: 87097 SS. Flow rate for a new pump is 36 gpm at max rpm of 600. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Pump currently has O-ring seals. Drive and pump seals can be changed to suit your application. SEW variable speed drive: 5 hp, 230/460 V, 13.6/6.6 amps, 60 Hz, 3 phase, Output: 37-216 rpm. Inlet: Flange with outside dimensions of 3 1/8 in. by 12 in., opening dimensions of 1 5/8 in. by 6 3/4 in. Outlet: 2 in. S-line fitting. Overall dimensions: 3 ft. 11 in. L x 2 ft. W x 3 ft. 3 in. H.











