

MRM 6 Head Manual Filler

Mfg: MRM

Model: MRM 35

Stock No. SLSP078.10

Serial No. 3322

MRM 6-Head Manual Filler. Model: MRM 35. S/N: 3322. Nozzle diameter: 1/2 in. Valves separation distance and height are adjustable. Maximum aperture/clearance: 6-1/2 in. W x 12 in. H. Infeed container dimensions: 19-7/8 in. L x 9-7/8 in. W x 15-7/8 in. H. Container capacity: 13 gal. Allen Bradley Photoswitch, Model: 42MRA-5000. Inlets: (1) 3/4 in. dia. infeed port, (1) 19-7/8 in. L x 9-7/8 in. W infeed. Outlets: (1) 2 in. dia. FNPT (drain). Overall dimensions: 63-1/2 in. L x 34 in. W x 94 in. H.





