

APV R-Series Positive Displacement Pump

Mfg: APV

Model: R6BS

Stock No: SMBS288.12

Serial No: PP-1986-0499

APV R-Series Positive Displacement Pump. Model: R6BS. S/N: PP-1986-0499. Flow rate for new pump is 120 gpm with required horsepower and pressure at 80 psi. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Reliance electric motor, 5 hp, 1745 rpm, 230/460 V, 12.4/6.2 amps, 60 Hz, 3 phase. Gear reducer ratio: 6.2. Final rpm: 282. Inputs/Outputs: (2) 3 in. S-line fittings. Overall dimensions: 4 ft. 2-1/4 in. L x 1 ft. 10-1/4 in. W x 2 ft. 1/2 in. H. (ACN110).





