

Jefferson Electric Transformer- 50 KVA

Mfg: Jefferson

Model:

Stock No. SNBB248.1

Serial No.

Jefferson Electric Transformer- 50 KVA. Cabinet Style, Dry-Type. 3 phase, 60 Hz, 480 high voltage, 208 low voltage, Insulation Class H, 150 C rise, 3.2 % impedance. Capacity at stages 1-6: 501 V, 490 V, 480 V, 470 V, 450 V, 449 V. Overall dimensions: 24 in. L x 21 in. W x 41 in. H.

