

Thermal Care Water Cooled Accuchiller- 30 Ton

Mfg: Thermal Care

Model: AQ1W2504

Stock No. SNBB337.45

Serial No. 92810019801

Thermal Care Water Cooled Accuchiller- 30 Ton. Model AQ1W2504. S/N 92810019801. Refrigerant: R-22. Min/max. temperature: 30/60 F. Copeland Compressor- 30 hp, Model: 4DH1-2500-TSK-206, S/N: ET97K02780S. US Electrical Motor: 10 hp, 3490 rpm, 208-230/460 V, 26.4/13.2 amps, 60 Hz, 3 phase. 1997 Dunham Bush Condensator, Model: CDR01037A21. Shell side: MAWP: 406 psi @ 200 °F; MDMT: 18 °F @ 406 psi. Tube side: MAWP: 250 psi @ 150 °F; MDMT: 18 °F @ 250 psi. Inlets/outlets: (3) 2 in. dia. pipes, (1) 3 in. dia. pipe with a 7-1/2 in. dia. flange and (4) attachment holes. Overall dimensions: 80 in. L x 34 in. W x 55 in. H.



