

Bingley Shell and Tube Heat Exchanger

Mfg: Bingley

Model:

Stock No. SNCC138.4

Serial No. 195

Bingley Shell and Tube Heat Exchanger. S/N: 195. Tube material: 304 stainless steel. Number of passes: 1. Number of tubes: 100. Tube dimensions: 1 in. dia. x 8 ft. L. Heat transfer surface area: 209.4 sq. ft. Tube volume: 32.6 gallons. Design pressure: 75 psi @ 100°F. Shell thickness: 1/4 in. Head thickness: 3/16 in. Inlets: (2) 4 in. dia. ports, (1) 2 in. dia. port. Outlets: (2) 4 in. dia. ports, (1) 1-1/2 in. dia. port. Overall dimensions: 9 ft. 10 in. L x 2 ft. 10 in. W x 2 ft. 7 in. H.



