

Stephan Microcut Emulsifier

Mfg: Stephan

Model: MCHD60-11/C

Stock No. SNPM047.11a

Serial No. 711.671.01

Stephan Microcut Emulsifier. Model: MCHD60-11/C. S/N: 711.671.01. Capacity: 8,500 lbs/hr (4000 kg/hr). The Stephan Microcut is a multifunctional fine cutting and dispersing system. Horizontal construction with double stage rotor-stator assembly. Benefits of the Microcut: efficient fine grinding, ideal cutting, homogenous mixing, optimal powder dispersing, stable emulsions, constant product quality, and ease of operation. Cutting disc diameter: 7 in. Stephan Motor, 100 hp (80 kW), 3560 rpm, 440 V, 137 amps, 60 Hz, 3 phase. Inlets: (1) 3 in. dia. S-line fitting. Outlets: (1) 3 in. dia. I-line fitting. Overall dimensions: 74 in. L x 33 in. W x 52 in. H.







