

GS Hevi-Duty Electric 118 KVA SCR Drive Transformer

Mfg: GS

Model:

Stock No. SNPM076.1a

Serial No. 203526

GS Hevi-Duty Electric 118 KVA SCR Drive Transformer. S/N: 203526. Specification: 0451522T00. Dry-type transformer. Percent impedance @ 338 °F: 5.2. Class: AA. Electrical requirements: 380 V (high), 460/266 V (low), 179 amps (high), 148 amps (low). Overall dimensions: 33 in. L x 21 in. W x 44 in. H.

