

## Reliance Electric MinPak Plus Variable Speed Drive- 10 HP

Mfg: Reliance

Model: 14C310

Stock No. SNPM102.2a

Serial No. 1GN4818.V21-UH

Reliance Electric MinPak Plus Variable Speed Drive- 10 HP. Model: 14C310. S/N: 1GN4818.V21-UH. Electrical requirements (AC input): 230 V, 36 amps (max), 50/60 Hz. Electrical requirements (DC out): 240 V, 38 amps, 3 phase. Overall dimensions: 14 in. L x 13 in. W x 31 in. H.

MinPak Plus drives offer standard features and options along with a variety of modification kits to tailor the drives to specific application requirements. MinPak drives include both single-phase drives in a NEMA 4 enclosure for 1/4-5 HP regenerative and non-regenerative applications and three-phase drives in NEMA 12 enclosures for 3-40 HP non-regenerative applications.

