

Viking DuraLobe Positive Displacement Pump

Mfg: Viking

Model: S2M

Stock No. SNSL265.12

Serial No. C13324

Viking DuraLobe Positive Displacement Pump. Model: S2M. S/N: C13324. 316 Stainless steel construction. Maximum capacity: 70 gpm at 1150 rpm. Maximum pressure: 150 psi. Working temperature range: -40°F to 300 °F. Seal option: Double mechanical seals. U.S. Motor, 3 hp, 230/460 V, 8.8/4.4 amps, 60 Hz. Motor drive. DuraLobe series' bi-wing rotor form minimizes slip, allows relatively high pressures, and also provides large voids for handling soft solids such as cherry pie filling. Pump inlet/outlet: 2 in. 'S' line. Overall dimensions: 3 ft. 7 in. L x 1 ft. 6 in. W x 1 ft. 3 in.



