

Viking Pump, Model S2M

Mfg: Viking

Model: S2M

Stock No. SNSL271.4

Serial No. 103063 A/95

Viking Pump. Model: S2M. S/N: 103063 A/95. US Motor: 3 hp, 1175 & 965 rpm, 208-230/460 & 190/380 V, 9.6-9.0/4.5 & 10.6/5.3 amps, 60 & 50 Hz. Motor drive. Maximum capacity: 70 gpm at 1150 rpm. Maximum pressure: 150 psi. Pump head: 316 stainless steel; mechanical seals. Temperature range: -40 to 300 °F. Pump inlet/outlet: 2 in. 'S' line. Overall dimensions: 51 in. L x 17 in. W x 18 in. H.





