

Spirax Sarco Pressure Powered Pumps

Mfg: Spirax Sarco

Model:

Stock No: SPGP023.1

Serial No:

(2) Spirax Sarco Pressure Powered Pumps. Type: PPC. Size: 2. B.M. No: 68547. Inspection No's: 718F96 and JSF96. Maximum pressure: 125 psi. Inlets: (1) 2 in. dia. liquid infeed port, (1) 1/2 in. dia. operating pressure port. Outlets: (1) 2 in. dia. liquid discharge port, (1) 1 in. dia. exhaust port, (1) 3/4 in. dia. drain port, (1) 1/2 in. dia. plug. Overall dimensions: 3 ft. 4 in. L x 1 ft. 9 in. W x 2 ft. 5 in. H (pump 1); 3 ft. 5 in. L x 1 ft. 7 in. W x 3 ft. H (pump 2).



