

## Viking Asphalt Series Internal Gear Pump

Mfg: Viking

Model: H32, HL32

Stock No. SPGP158.1

Serial No. 10854122, 10854127 and 10798560

(3) Viking Asphalt Series Internal Gear Pumps. Models: H32 and HL32\*. S/N's: 10854122, 10854127 and 10798560\*. Nominal capacity at maximum speed: 20 gpm. Maximum speed: 1200 rpm. Maximum pressure: 100 psi. The Asphalt Pump series are economical General Purpose pumps utilizing a "floating" rotor design. The jacketed head and rotor bearing sleeve are designed to allow passage of saturated steam or heat transfer fluid to melt asphalt that has solidified in the pump prior to startup. Inlets/outlets: (2) 1 in. dia NPT (female), (2)\* 1-1/2 in. dia. NPT (female). Overall dimensions: 12 in. L x 5-1/2 in. W x 6 in. H. Note: (\*) Represents Viking pump HL32 which has 1-1/2 in. ports.

