Cherry Burrell Stellar Series High Pressure Pump / Homogenizer	
Mfg: Cherry Burrell	Model:
Stock No: SPGT015.10	Serial No:

Cherry Burrell Stellar Series High Pressure Pump / Homogenizer. Single stage. Plunger Size: 1-1/2 in. diameter. Poppet seat valve cylinders. Brook Crompton electric motor, 40 hp, 1765 rpm, 575 V, 39.0 amps, 60 Hz, 3 phase. Driver pulley: 4-1/4 in. dia. Driven pulley: 24 in. dia. Ratio: 5.65. Final rpm: 312. Inlets: (2) 2 in. diameter I-Line fitting. Outlets: (1) 7/8 in. MNPT. Overall dimensions: 3 ft. 10 in. L x 3 ft. W x 4 ft. 4 in. H.









































































