

Resina Pneumatic Screw Capper

Mfg:

Model: S

Stock No. SPPP248.1

Serial No. 561621

Resina Pneumatic Screw Capper. Model: S, S/N: 56 1621. Century motor, ½ hp, 1735 rpm, 220/440 V, 1.5/0.75 amps, 60 Hz, 3 phase. Set for 38 mm (1.5 in.) metal caps. Conveyor dimensions: 62 in. L x 4-1/2 in. W. One capping head. Container feeder dimensions: 24 in. L x 18 in. W and slope from 12-1/2 in. H. to 19 in. H. Rotation cap feeder system: 20 in. diameter. Overall dimensions: 63 in. L x 30 in. W x 85 in. H.



