

Magnetek Control Panel

Mfg: Magnetek

Model:

Stock No. SSLP1012.2a

Serial No.

Magnetek Control Panel. Westinghouse motor operator for AB De-ion circuit breaker, type: HMC, volts: 120 VAC, frequency: 60 Hz, Style: 5664D54G75. (3) Westinghouse controllers, type: IMC CURR transfer, 0.6 KV to 10 KV, 1.33 amps RF. (2) LR instrument transformers, type: 460, ratio: 4 to 1. PRI: 480 V, CAT: 460-480 V, 50 & 60 Hz. Electro Industries, Model: KWP 211, S/N: 883563. Power input: 135 VAC, 150 V, CUR 1A, CT ratio: 800/1, PT ratio: 480/120, frequency: 47-440. (3) Solid state protective voltage relays. (3) ATC variable ranges: 1 min, 10 min, 10 sec. (3) Gauges: AC amps 0-800, kilowatts 0-600, AC volts 0-600. Overall dimensions: 36 in L x 21 in. W x 91 in. H.



