

## Waukesha 25 Positive Displacement Pump

Mfg: Waukesha

Model: 25DO

Stock No. SSPN123.4a

Serial No. DO44913SS

Waukesha 25 Positive Displacement Pump. Model: 25DO. S/N: DO44913SS. Pumping capacity (maximum): 35.6 gpm. Pumping capacity (minimum): 11.52 gpm. Displacement per revolution: 0.060 gallons. Nominal capacity: 36 gpm. Pressure range: 150 psi. Maximum rpm: 600. Reliance Electric Motor, 2 hp, 240 V. Reeves Variable Speed Module, size: 221, ratio: 5.06, 594 rpm (max), 192 rpm (min). A-3 sanitary rated. Single o-ring seals. 316 stainless steel body, cover and shafts. Components can be easily disassembled for COP cleaning. Ideal for the following industries: bakery, beverage, canning, confectionary, cosmetics, dairy, meat packing, pharmaceutical and aseptic. Inlets/outlets: (2) 1-1/2 in. dia. S-line fittings. Overall dimensions: 38-1/2 in. L x 15 in. W x 31-1/2 in. H.



