

## APV Crepaco R3 Positive Displacement Pump

Mfg: APV Crepaco

Model: R3R

Stock No.: SUBF606.3

Serial No.: R3R-25603

APV Crepaco Positive Displacement Pump. Model: R3R. Flow rate for new pump is 40 gpm with required horsepower and pressure. Discuss with salesperson your process and duty to determine if this refurbished pump should handle your specific duty. Baldor electric motor, 5 hp, 1725 rpm, 208-230/460 V, 15.0-13.2/6.6 amps, 60 Hz, 3 phase. Sterling Electric Speed-Trol® variable speed drive. Gear ratio: 5.06:1. Input rpm 1,725. Final rpm range: 90 rpm to 340 rpm. Inlet/Outlet: (2) 1-½ in. ACME fittings. Mounted on a carbon steel base. Overall dimensions: 4 ft. 2 in. L x 1 ft. 3 in. W x 2 ft. 6 in. H.(ACN74).





