

2002 Alfa Laval Plate Heat Exchanger – 16.57 Sq. Ft.

Mfg: Alfa Laval

Model: M6-MFG

Stock No: TACJ0823.6

Serial No: 30104-84515

Alfa Laval Plate Heat Exchanger. Model: M6-MFG. S/N: 30104-84515. MAWP: 150 psi at 221 °F. MDMT: -20 °F at 150 psi. (13) Total plates. Plate dimensions: 9-1/2 in. W x 2 ft. 5-1/2 in. H. Effective heat transfer area: 16.57 sq. ft. Spirax Sarco Inc. Flash recovery vessel. Certified by John Wood Co. Built in 2001. MAWP: 150 psi at 500 °F. Vessel dimensions: 12 in. dia. x 2 ft. 5-1/8 in. straight wall (15.5 gals.) Inlets/Outlets: (2) 5-1/4 in. flange dia. with (8) 7/8 in. mounting holes, 3-1/4 in. adjacent, 8-3/8 in. opposite. (3) 2 in. MNPT. (1) 1-1/2 in. MNPT. (1) 1-5/8 in. port. Overall dimensions: 5 ft. 11-1/8 in. L x 2 ft. 2-3/4 in. W x 6 ft. 1 in. H.



