

Burton Corbin Reciprocating Gas Compressor

Mfg: Burton Corbin

Model: P123-M82S

Stock No.: TAFM065.7a

Serial No.: 26990

1990 Burton Corbin Reciprocating Gas Compressor. Model: P123 M82S. S/N: 26990. ABB electric motor, 30 hp, 1760 rpm, 440 V, 37 amps, 60 Hz, 3 phase. Applications include inert gases such as Nitrogen or Hydrogen. Inlets: (1) 1 in. dia. NPT fittings, (1) 2 in. dia. flanged port. Outlets: (1) 2 in. dia. flanged port. Overall dimensions: 7 ft. 7 in. L x 4 ft. 11 in. W x 4 ft. 7 in. H.(ACN1000).





