

2000 Teledyne Laars Mighty Therm Gas-Fired Hot Water Boiler- 60 HP

Mfg: Teledyne Laars

Model: HH2450IN18KCAAEX

Stock No.: THHS002

Serial No.: C00B01803

2000 Teledyne Laars Mighty Therm Gas-Fired Hot Water Boiler- 60 HP. Model: HH2450IN18KCAAEX. S/N: C60B01803. Nat'l Bd: 97573. Maximum input: 2,450,000 Btuh. Minimum input: 735,000 Btuh. Output: 2,009,000 Btuh. Minimum relief valve capacity: 2,450 lbs/hr. Maximum working pressure: 160 psi. Bell & Gossett Pump, Model: 5-125, S/N: 80-3X3X7B. Baldor Industrial Motor, 1-1/2 hp, 1725 rpm, 208-230/460 V, 5.4-8/2.4 amps, 60 Hz, 3 phase. Watts pressure relief valve, Model: M, S/N: 99520, Size 1 in., set 75 lb, Btuh rating: 2,649,000. McDonnell flow switch, Model: FS4-3. Honeywell gas valve. Inlets: (1) 1-1/2 in. dia. NPT (male, gas), (1) 4 in. dia. port with ASME 125lb. flange. Outlet: (1) 1 in. dia. copper pipe (pressure relief), (1) 4 in. dia. port with ASME 125 lb. flange. Overall dimensions: 8 ft. 8 in. L x 4 ft. 6-1/2 in. W x 5 ft. 10 in. H.



