

2000 Teledyne Laars Mighty Therm Gas-Fired Hot Water Boiler- 60 HP

Mfg: Teledyne Laars Heating Systems

Model: HH2450IN18KCAEX

Stock No.: THHS003

Serial No.: C00B01802

2000 Teledyne Laars Mighty Therm Gas-Fired Hot Water Boiler- 60 HP. Model: HH2450IN18KCAEX. S/N: C00B01802. Nat'l Bd: 97573. Maximum input: 2,450,000 Btuh. Minimum input: 735,000 Btuh. Output: 2,009,000 Btuh. Minimum relief valve capacity. 2,450 lbs/hr. Maximum working pressure 160 PSI. McDonnell flow switch, Model: FS4-3. Honeywell gas valve. Baldor Motor. 1-1/2 Hp. 1725 Rpm. 208-230/460 Volts. 5.4-8/2.4 Amps. 60 Hz. 3 Phase. Frame 145JM. Bell & Gossett Pump, Model: 5-125, S/N: 14F006. Watts regulator valve, Model: M, S/N: 99520, Btuh rating: 2,649,000. Size 1 In. Set 75 lb. Inlets: (1) 1-1/2 in. dia. NPT (male, gas), (1) 4 in. dia. port with ASME 125 lb. flange. Outlet: (1) 1 in. dia. copper pipe (pressure relief), (1) 4 in. dia. port with ASME 125 lb. flange. Overall dimensions: 8 ft. 8 in. L x 4 ft. 6-1/2 in. W x 5 ft. 10 in. H.

