

Stafsjö 18 in. Knife Gate Valve

Mfg: Stafsjö

Model: T-MVU 450 / 77

Stock No: TMCB169

Serial No:

Stafsjö 18 in. knife gate valve. Model: T-MVU450 / 77. Motor: 0.164 H.P, 115 V, 1725 RPM, single phase, 60 Hz. Output RPM: 17. Output torque: 55 FT-LBS. Overall dimensions: 2 ft. 2 in. L x 1 ft. 8 in. W x 6 ft H.





posi-tork®			
andco actuator products, inc.			
BUFFALO, N.Y., U.S.A.			
MODEL	ARI-25S	TORQUE RATING	55 FT.-LBS.
ORDER	3700200	OUTPUT R.P.M.	17
SERIAL NO.	10055		
MOTOR DATA			
SIZE	25S	R.P.M.	1725
H.P.	.164	PHASE	1
AMB.	40C	FRAME	42
FLA.	4.1	VOLTS	115
		DUTY	25
		INSUL.	B
		FREQ.	60



STAFS 46 BRUK SVEDEN
T-MVU 450/17

WARNING
DISCONNECT SUPPLY CABLES
KEEP COUPLER TIGHTLY CLOSED
READ INSTRUCTIONS BEFORE OPERATION
EQUIPEMENT A LA COURSE
LES ENCLAIS DOIVENT ETRE
DECOUPLÉS AVANT L'ARRÊT
ANDCO ACTUATOR PRODUCTS, INC.
BUFFALO, N.Y.