

Mycom 8 Cylinder Reciprocating Ammonia Compressor - 150 HP

Mfg: Mycom

Model: N8B

Stock No: TMCB299.5

Serial No: 11021

Mycom 8 Cylinder Reciprocating Ammonia Compressor. Model: N8B. S/N: 11021. Refrigerant: R-717 (Ammonia). Displacement: 450 cfm. LEAK (Psig) HP: 313. LP: 185 HYD (Psig) HP: 470. LP: 470. Lincoln electric motor: S/N: 1303404. 150 hp, 460 V, 60 Hz, 1780 rpm, 3 phase, 169 A. Overall dimensions: 8 ft. L X 4 ft. 7 in. W X 4 ft. 3 in. H.





