

Dunham Bush Water Cooled Indoor Chiller - 40 Ton

Mfg: Dunham-Bush

Model: WC40A

Stock No: TPM03

Serial No: 81014001A86E

Dunham Bush Water Cooled Indoor Chiller- 40 Ton. Model: WC40A. S/N: 81014001A86E. Refrigerant: R-22. Design pressure: 300 psig high, 235 psig low. Control panel: 115 V, 3 phase, 60 Hz. Min. circuit ampacity: 74; max fuse size: 125. Copeland compressor, Model: 6DS14000TXN, 40 hp, RLA: 59, LRA: 300. Electrical requirements: 460 V, 3 phase, 60 Hz. Crankcase heater: 200 W, FLA: 1.7, 115 V, 1 phase, 60 Hz. Chiller barrel dimensions: 9 in. dia. x 6 ft. 10 in. L. Insulated condenser barrel dimensions: 9 in. dia. x 5 ft. 9 in. L. Overall dimensions: 7 ft. 8 in. L x 3 ft. W x 3 ft. 7 in. H. (ACN220).



