

Videojet Ink Jet Marking Machine 37Plus

Mfg: Videojet

Model: 37Plus

Stock No. TMSG001.12

Serial No. E496L24006

Videojet Ink Jet Marking Machine. Model 37Plus. S/N E496L24006. Line Speed Capability: 5x7 matrix, single line: 300 ft./min. (91 m/min.) 5x7 matrix, twin line: 209 ft./min. (64 m/min.); 7x9 matrix, single line: 223 ft./min. (68 m/min.); 10x16 matrix, single line: 209 ft./min. (64 m/min.). Speeds for 5x7 and 7x9 matrix based on 10 characters per inch (4 characters per cm); 10x16 matrix speed based on 5 characters per inch (2 characters per cm). Print Rate: 37plus: Up to 837 characters per second (twin line) and 600 characters per second (single line). Electrical Requirements: 100-240 VAC, 1.0 amps, 50/60 Hz. Power consumption 30 watts maximum. Overall dimensions: 32 in. L x 24 in. W x 74 in. H.



