

1992 APV Stainless Steel Jacketed Processor Tank-500 Gallons

Mfg: APV

Model:

Stock No. UGHB009.

Serial No. G-8495

1992 APV Stainless Steel Jacketed Processor Tank-500 Gallons. S/N: G-8495. Natd Bd No. 8232. Inside straight wall dimensions: 4 ft. 2 in. dia. x 4 ft. 6 in. H. MAWP: 75 psi @ 350°F. MDMT: 75 psi @ -20°F. Reliance Electric Motor, 2 hp, 1740 rpm, 460 V, 2.9 amps, 3 phase. Reliance Gearmotor, ratio: 86, rpm out: 20 (final). Maximum number of scrapers: 8. Scraper dimensions: 3-1/2 in. W x 10 in. L. Blade dimensions: 6 in. W x 2 ft. 1 in. L. Baffle dimensions: 9 in. W x 2 ft. L. Inlets: (2) 3 in. dia. S-line fittings, (1) 1 in. dia. ACME fittings, (1) 2-1/2 in. dia. S-line fittings, (2) 2 in. dia. FNPT fittings (steam in). Outlets: (1) 2-1/2 in. dia. port, (2) 2 in. dia. FNPT fittings (steam out). Overall dimensions: 6 ft. L x 4 ft. 8 in. W x 8 ft. 6 in. H.





