

St. Regis / Crepaco 700R Positive Displacement Pump Stainless Steel Head

Mfg: St. Regis / Crepaco

Model: 700R

Stock No. W-19

Serial No. 8976

St. Regis / Crepaco 700R Positive Displacement Pump Stainless Steel Head. S/N: 8976. Pump maximum capacity: 200 gpm at 400 rpm, (4) Standard recessed face rotors. The 700R series is designed for applications where long discharge lines and/or viscous products combine to create high head pressures. These pumps are equipped with external outboard bearings to prevent shaft deflections and minimize shaft, rotor, and seal wear, is recommended for discharge pressures between 100 and 150 psi. U.S. Variable motor drive, 10 hp, 1800 rpm, 220/440 V, 33.1/46.55 amps, 60 Hz, 3 phase. Pump inlets/outlets: 4 in. threaded fittings. Overall dimensions: 80 in. L x 24 in. W x 41 in. H.



