

Breddo Likwifier 50 gallons, Model LDT-50, S/N 986630127053, 15 hp, 1765 rpm, 3 ph, 60 hz, 230/460 volt, 59/19.5 amp, 1,800 rpm waferthin motor, TEFC, (2) 2 in. tri-clamp inlets, (1) 2-1/2 in. tri-clamp outlet, (1) 18 in. round manway and gasket, 10 in. threaded impeller, (4) 2 in. Schedule 40 pipe legs for tank support with adjustable ball feet. Surfaces 12 gauge all 304 stainless construction. Dimensions 24-1/2 in. square tank. Overall dimensions 26 in. L x 26 in. W x 56 in. H.

